



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HS14C 7/32" High Speed Steel Drill (Carded)

L.H. Dottie CO.

Catalog Number	HS14C
Manufacturer	L.H. Dottie CO.
Description	High Speed Drill, M2 Grade, Steel Material, Black/Gold Finish, Split Point Type, 135 Deg Split Drill Point, 7/32 In. Fractional Size, 3-3/4 In. Overall Length, 3/16 In. Shank Diameter, Carded 2 Pieces
Weight per unit	0.1000 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Grade	M2
Material	High Speed Steel
Number of Pieces	2
Point Type	Split Point
Shank Diameter	3/16

Material, Color, and Finish

Finish	Black/Gold
--------	------------

Dimensions and Weight

Overall Length	3-3/4
----------------	-------

Descriptions

Description	7/32" HIGH SPEED STEEL DRILL (CARDED)
extra long description	DOTTIE HS14C Carded 2 pack - 7/32"
Long Description	High Speed Drill, M2 grade, Steel material, Black/Gold finish, Split Point Type, 135 DEG Split drill point, 7/32 in. fractional size, 3-3/4 in. overall length, 3/16 in. shank diameter, Carded 2 pieces
Product Type	Carded 2 Pack - 7/32" High Speed Steel Drills
Special Features	Features: Industrial Quality, Heavy Duty Jobber Length, Fractional Sizes

Manufacturer Information

Brand	LH DOTTIE
GTIN	00781002821342
Manufacturers Part Number	HS14C
UPC	781002821342

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	High Speed Drill

Packaging

Carton	1
Weight Per each	0.1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application For Steel, Steel Forging, Cast Iron and Other Work Materials