



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HS28C 7/16" High Speed Steel Drill (Carded)

L.H. Dottie CO.

Catalog Number	HS28C
Manufacturer	L.H. Dottie CO.
Description	High Speed Drill, M2 Grade, Steel Material, Black/Gold Finish, Split Point Type, 135 Deg Split Drill Point, 7/16 In. Fractional Size, 5-1/2 In. Overall Length, 3/16 In. Shank Diameter, Carded 1 Piece
Weight per unit	0.2000 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Grade	M2
Material	High Speed Steel
Number of Pieces	1
Point Type	Split Point
Shank Diameter	3/16

Material, Color, and Finish

Finish	Black/Gold
--------	------------

Dimensions and Weight

Overall Length	5-1/2
----------------	-------

Descriptions

Description	7/16" HIGH SPEED STEEL DRILL (CARDED)
extra long description	DOTTIE HS28C Carded 1 pack - 7/16"
Long Description	High Speed Drill, M2 grade, Steel material, Black/Gold finish, Split Point Type, 135 DEG Split drill point, 7/16 in. fractional size, 5-1/2 in. overall length, 3/16 in. shank diameter, Carded 1 piece
Product Type	Carded 1 Pack - 7/16" High Speed Steel Drills
Special Features	Features: Industrial Quality, Heavy Duty Jobber Length, Fractional Sizes

Manufacturer Information

Brand	LH DOTTIE
GTIN	00781002821489
Manufacturers Part Number	HS28C
UPC	781002821489

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	High Speed Drill

Packaging

Carton	1
Weight Per each	0.2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application For Steel, Steel Forging, Cast Iron and Other Work Materials