



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

HS32 1/2" High Speed Steel Drill

L.H. Dottie CO.

Catalog Number	HS32
Manufacturer	L.H. Dottie CO.
Description	High Speed Drill, M2 Grade, Steel Material, Black/Gold Finish, Split Point Type, 135 Deg Split Drill Point, 1/2 In. Fractional Size, 6 In. Overall Length, 3/16 In. Shank Diameter, 1 Piece
Weight per unit	0.2830 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Grade	M2
Material	High Speed Steel
Number of Pieces	1
Point Type	Split Point
Shank Diameter	3/16

Material, Color, and Finish

Finish	Black/Gold
--------	------------

Dimensions and Weight

Overall Length	6
----------------	---

Descriptions

Description	1/2" HIGH SPEED STEEL DRILL
extra long description	DOTTIE HS32 1/2" High Speed Steel D
Long Description	High Speed Drill, M2 grade, Steel material, Black/Gold finish, Split Point Type, 135 DEG Split drill point, 1/2 in. fractional size, 6 in. overall length, 3/16 in. shank diameter, 1 piece
Product Type	1/2" High Speed Steel Drills
Special Features	Features: Industrial Quality, Heavy Duty Jobber Length, Fractional Sizes

Manufacturer Information

Brand	L.H. Dottie CO.
GTIN	00781002293323
Manufacturers Part Number	HS32
UPC	781002293323

Taxonomies, Classifications, and Categories

Category Description	TOOL BAG/POUCHES
Type	High Speed Drill

Packaging

Carton	1
Weight Per each	0.283



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application For Steel, Steel Forging, Cast Iron and Other Work Materials