



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

HS8 1/8" High Speed Steel Drill

L.H. Dottie CO.

| | |
|------------------|--|
| Catalog Number | HS8 |
| Manufacturer | L.H. Dottie CO. |
| Description | High Speed Drill, M2 Grade, Steel Material, Black/Gold Finish, Split Point Type, 135 Deg Split Drill Point, 1/8 In. Fractional Size, 2-3/4 In. Overall Length, 3/16 In. Shank Diameter |
| Weight per unit | 0.0080 (lbs/each) |
| Product Category | Bits, Parts, Accessories |

Features

| | |
|------------------|------------------|
| Grade | M2 |
| Material | High Speed Steel |
| Number of Pieces | 4 |
| Point Type | Split Point |
| Shank Diameter | 3/16 |

Material, Color, and Finish

| | |
|--------|------------|
| Finish | Black/Gold |
|--------|------------|

Dimensions and Weight

| | |
|----------------|-------|
| Overall Length | 2-3/4 |
|----------------|-------|

Descriptions

| | |
|------------------------|--|
| Description | 1/8" HIGH SPEED STEEL DRILL |
| extra long description | DOTTIE HS8 1/8" High Speed Steel Dr |
| Long Description | High Speed Drill, M2 grade, Steel material, Black/Gold finish, Split Point Type, 135 DEG Split drill point, 1/8 in. fractional size, 2-3/4 in. overall length, 3/16 in. shank diameter |
| Product Type | 1/8" High Speed Steel Drills |
| Special Features | Features: Industrial Quality, Heavy Duty Jobber Length, Fractional Sizes |

Manufacturer Information

| | |
|-------|-----------------|
| Brand | L.H. Dottie CO. |
| GTIN | 00781002293088 |
| UPC | 781002293088 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------|
| Category Description | TOOL BAG/POUCHES |
| Type | High Speed Drill |

Packaging

| | |
|-----------------|-------|
| Carton | 12 |
| Weight Per each | 0.008 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | For Steel, Steel Forging, Cast Iron and Other Work Materials |
|-------------|--|