



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HSTT3848QC HT Shrink Tubing Panduit Corporation

Catalog Number	HSTT3848QC
Manufacturer	Panduit Corporation
Description	Thin Wall Shrink Tube, Polyolefin Material, Clear, 600 V, 0.187 In; 4.8 MM Recovered Diameter, 0.375 In Expanded Diameter, 2:1 Shrink Ratio, -67 °F Operating Temperature, +275 °F Operating Temperature, 4 FT Length, 0.025 In Thickness
Weight per unit	1.7 (lbs/each)
Product Category	Insulating Materials

Features

continuous operating temperature	275
flammability	N/A
Inside Diameter	0.187
media	Yes
outside diameter	0.375

Descriptions

Description	HT SHRINK TUBING
extra long description	PAN HSTT38-48-QC Dry-Shrink™ HSTT38

Manufacturer Information

Brand	PANDUIT
GTIN	00074983906635
UPC	074983906635

Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	Heat-Shrink Tubing

Packaging

Carton	25
Weight Per each	1.66

Uses, Certifications, and Standards

Application	For Dry Locations
standard	UL Recognized, CSA Approved, MIL SPEC