



I17XXFLEX30004PK Fluke-17XX Iflexi 3000A 24", 4PK

Fluke Electronics

Catalog Number	I17XXFLEX30004PK
Manufacturer	Fluke Electronics
Description	Fluke 24 Inch Iflex Flexible Current Probes Measure to 3000A Ac While Providing The Ultimate Measurement Flexibility. The Iflex Probes Connect Directly to The Energy Logger, Displaying Current Measurements Without Error Prone Scaling Factors. The 1.8 M (6 FT) Cord Allows Separation Between The Measurement Location and The Energy Logger Making It Easier to View The Display. 4-Pack
Weight per unit	2.4 (lbs/each)
Product Category	Meters, Panel Instruments

Descriptions

Description	FLUKE-17XX IFLEXI 3000A 24", 4PK
extra long description	FLK I17XX-FLEX3000/4PK FLEX CURRENT
Long Description	Fluke 24 inch iFlex flexible current probes measure to 3000A AC while providing the ultimate measurement flexibility. The iFlex probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. 4-pack
Product Type	Flex Current Probe, 3000A, 4PK

Manufacturer Information

Brand	Fluke Electronics
GTIN	00095969786768
Manufacturers Part Number	I17XX-FLEX3000/4PK
UPC	095969786768

Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
----------------------	---

Packaging

Carton	1
Weight Per each	2.4