

Specifications

Eaton I52

Eaton strain relief I-Grip,
0.52-0.73" cord diameter,
7.00" mesh length,
Galvanized Steel

Product specifications

TYPE	Strain relief I-Grip
CORD DIAMETER	0.52-0.73 in
MATERIAL	Galvanized Steel
MESH LENGTH	7.00 in

General specifications

PRODUCT NAME	Eaton strain relief I-Grip
CATALOG NUMBER	I52
UPC	040893650906
PRODUCT LENGTH/DEPTH	8 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	2.5 in
PRODUCT WEIGHT	0.04 lb
CERTIFICATIONS	CSA Certified



Powering Business Worldwide

Specifications

Eaton I52

Eaton strain relief I-Grip,
0.52-0.73" cord diameter,
7.00" mesh length,
Galvanized Steel

Product specifications

TYPE	Strain relief I-Grip
CORD DIAMETER	0.52-0.73 in
MATERIAL	Galvanized Steel
MESH LENGTH	7.00 in

General specifications

PRODUCT NAME	Eaton strain relief I-Grip
CATALOG NUMBER	I52
UPC	040893650906
PRODUCT LENGTH/DEPTH	8 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	2.5 in
PRODUCT WEIGHT	0.04 lb
CERTIFICATIONS	CSA Certified



Powering Business Worldwide