

# Specifications

## Eaton I70

Eaton strain relief I-Grip,  
0.70-0.85" cord diameter,  
8.50" mesh length,  
Galvanized Steel

### Product specifications

<b>TYPE</b>	Strain relief I-Grip
<b>CORD DIAMETER</b>	0.70-0.85 in
<b>MATERIAL</b>	Galvanized Steel
<b>MESH LENGTH</b>	8.50 in

### General specifications

<b>PRODUCT NAME</b>	Eaton strain relief I-Grip
<b>CATALOG NUMBER</b>	I70
<b>UPC</b>	040893650913
<b>PRODUCT LENGTH/DEPTH</b>	10.5 in
<b>PRODUCT HEIGHT</b>	0.75 in
<b>PRODUCT WIDTH</b>	2.5 in
<b>PRODUCT WEIGHT</b>	0.055 lb
<b>CERTIFICATIONS</b>	CSA Certified



*Powering Business Worldwide*

# Specifications

## Eaton I70

Eaton strain relief I-Grip,  
0.70-0.85" cord diameter,  
8.50" mesh length,  
Galvanized Steel

### Product specifications

<b>TYPE</b>	Strain relief I-Grip
<b>CORD DIAMETER</b>	0.70-0.85 in
<b>MATERIAL</b>	Galvanized Steel
<b>MESH LENGTH</b>	8.50 in

### General specifications

<b>PRODUCT NAME</b>	Eaton strain relief I-Grip
<b>CATALOG NUMBER</b>	I70
<b>UPC</b>	040893650913
<b>PRODUCT LENGTH/DEPTH</b>	10.5 in
<b>PRODUCT HEIGHT</b>	0.75 in
<b>PRODUCT WIDTH</b>	2.5 in
<b>PRODUCT WEIGHT</b>	0.055 lb
<b>CERTIFICATIONS</b>	CSA Certified



*Powering Business Worldwide*