



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IC1 4" Incandescent Ic Recess

*Lithonia Lighting - Acuity*

Catalog Number	IC1
Manufacturer	Lithonia Lighting - Acuity
Description	The Ic-Rated Incandescent New Construction Housing Features An Air-Loc Seal to Stop Infiltration and Ex Filtration Of Air. This Reduces Heating and Cooling Costs. The Socket Is Medium Base Porcelain With A Nickel-Plated Copper Screw Shell.
Weight per unit	3.0 (lbs/each)
Product Category	Incandescent Recessed Architec

### Features

dimensions	9.125 x 6.0 x 6.125
Hardware	Yes
Lamp Type	Incandescent
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round
Voltage Rating	120

### Material, Color, and Finish

Color	Unfinished
-------	------------

### Dimensions and Weight

Height	6
Length	12.25
Width	13.25

### Descriptions

Construction	New Construction
Description	4" INCANDESCENT IC RECESS
extra long description	LITH IC1 4IN Incandescent New Const
Features	Contractor Select
Long Description	The IC-rated incandescent new construction housing features an Air-Loc seal to stop infiltration and ex filtration of air. This reduces heating and cooling costs. The socket is medium base porcelain with a nickel-plated copper screw shell.
Product Type	Housing



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	JUNO
GTIN	00661209700001
UPC	661209700001

## Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	Housing

## Trade Size

aperture size	4 in
---------------	------

## Packaging

Carton	1
Weight	4
Weight Per each	3

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	Indoor
Mounting	Recessed