



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC23W 6" RCS DBL Wall Housing, No Bracket

Lithonia Lighting - Acuity

Catalog Number	IC23W
Manufacturer	Lithonia Lighting - Acuity
Description	Incandescent Airtight Housing, Round, 90 W, 120 V, Galvanized, Steel Fixture Material, Aluminum Housing Material, Non Dimmable, 6 In Aperture Size, 19 LB
Weight per unit	19.0 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Number of Lamps	1
Shape	Round

Dimensions and Weight

Height	7.75
Length	13.5
Width	17.5

Descriptions

Construction	New Construction
Description	6" RCS DBL WALL HOUSING, NO BRACKET
extra long description	LITH IC23 W 6IN Incandescent No Pla

Manufacturer Information

Brand	JUNO
GTIN	00661209068613
Manufacturers Part Number	IC23 W
UPC	661209068613

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	Housing

Packaging

Carton	1
Package	6
Weight Per each	19

Uses, Certifications, and Standards

environmental conditions	Indoor
Mounting	Recessed
standard	CSA,UL