



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC928W Super Slope Ic HSG Wego *Lithonia Lighting - Acuity*

Catalog Number	IC928W
Manufacturer	Lithonia Lighting - Acuity
Description	This Slope Ceiling Ic Housing Is Energy Efficient. When Used With Air-Loc Gasket, It Stops Infiltration and Exfiltration Of Air. This Reduces Heating and Cooling Costs.
Weight per unit	4.5 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Hardware	Yes
Lamp Type	Incandescent
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	OVAL
Voltage Rating	120

Material, Color, and Finish

Color	Unfinished
-------	------------

Dimensions and Weight

Height	7
Length	18.5
Width	13.5

Descriptions

Construction	New Construction
Description	SUPER SLOPE IC HSG WEGO
extra long description	LITH IC928 W 6IN Incandescent Super
Long Description	This Slope ceiling IC Housing is energy efficient. When used with Air-Loc Gasket, it stops infiltration and exfiltration of air. This reduces heating and cooling costs.
Product Type	Housing

Manufacturer Information

Brand	JUNO
GTIN	00661209107817
Manufacturers Part Number	IC928 W
UPC	661209107817

Trade Size

aperture size	6 in
---------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight	4
Weight Per each	4.47

Uses, Certifications, and Standards

Application	Education, Government, Healthcare, Hospitality, House of Worship, Offices & Banks, Residential, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSA, UL