

VAPORTIGHT

[Ceiling / Pendant / Wall Mount]



ICVC1G



ICVP1G



ICVW1G



H.I.D.



CFL

WATTAGE	SOURCE	STOCK#	DIMENSIONS [H x W]
INCANDESCENT			
Ceiling Mount			
Up to 200W	INCAN.	ICVC1G ¹	9 3/4" x 4 1/4"
Up to 300W	INCAN.	ICVC2G ¹	11 1/2" x 5 11/16"
Pendant Mount			
Up to 200W	INCAN.	ICVP1G ¹	10 1/4" x 4 1/4"
Up to 300W	INCAN.	ICVP2G ¹	12 1/8" x 5 11/16"
Wall Mount			
Up to 200W	INCAN.	ICVW1G ¹	12 5/8" x 9 1/2"
Up to 300W	INCAN.	ICVW2G ¹	14 1/4" x 10 9/16"
METAL HALIDE			
Ceiling Mount			
70W	MH	MHVS-C-GG-70-MT-LL ²	12" x 8 1/2"
100W	MH	MHVS-C-GG-100-MT-LL ²	12" x 8 1/2"
COMPACT FLUORESCENT			
Ceiling Mount			
42W	CFL	PLVS-C-GG-42-UNV-LL ³	12" x 8 1/2"

NOTE: 1 Wired 120V. 2 Standard Multi-tap ballast 120/208/240/277V wired 277V. 3 "UNV" designates 120-277V.

For complete Lumark product information including specifications, photometry, and technical support please visit www.cooperlighting.com.

CATALOG NUMBER	DESCRIPTION	
-------------------	-------------	--

LOW-BAYS



DIRECT-MOUNT BALLAST HOUSINGS
MHLX-400-MT
MHLX-400-MT-OR
ACRYLIC REFRACTOR
PD22-XB/LX
PD25
ENCLOSURES
SGB22
SGB25
DB22
CB22
DB25
WIRE GUARDS
WG22
WG22/SGB
WGD22
LAMPS
METAL HALIDE
M58PG-250FG
M59PJ-400/UFG

400W MH Multi-Tap
400W MH Multi-Tap w/Open Rated Socket

22" Acrylic High-Bay Refractor for Direct Mounting
25" Acrylic High-Bay Refractor

22" Safety Glass Bottom
25" Safety Glass Bottom
22" Drop Acrylic Lens
22" Conical Acrylic Lens
25" Drop Acrylic Lens

22" Wire Guard
22" Gym Wire Guard w/Safety Glass Bottom
22" Wire Guard For Use w/Drop Lens

250W MH BT-28 Clear Mogul-Base
400W MH BT-37 Clear Mogul-Base

VERTIMARK II



HIGH PRESSURE SODIUM
HPBE-5A-100H-MT-LL
HPBE-5A-150H-MT-LL
METAL HALIDE
MHBE-5A-175H-MT-LL
MHBE-5A-250H-MT-LL

100W HPS Multi-Tap w/Lamp
150W HPS Multi-Tap w/Lamp

175W MH Multi-Tap w/Lamp
250W MH Multi-Tap w/Lamp

ACCESSORIES

HOOK, CORD AND PLUGS

FH-1
FL-1
SHK
PHC/3

PC3-120V
PC3-208V
PC3-240V
PC3-277V
PC3-480V

Hook
Loop
Hook w/Safety Screw
3' Power Cord and non-Nema Plug For Use with TPPH Mountings

3' Cord with NEMA 120V L5-15P Plug
3' Cord with NEMA 208V L6-15P Plug
3' Cord with NEMA 240V L6-15P Plug
3' Cord with NEMA 277V L7-15P Plug
3' Cord with NEMA 480V L8-20P Plug

MOUNTING BOXES

TWMB5
TPPH-120V-WHT

TPPH-208V-WHT

TPPH-277V-WHT

TPPH-480V-WHT

Thru-way Mounting Box For Steeler Housings Only
120V Thru-way Pendant Power Hook w/non-NEMA Receptacle

208V Thru-way Pendant Power Hook w/non-NEMA Receptacle

277V Thru-way Pendant Power Hook w/non-NEMA Receptacle

480V Thru-way Pendant Power Hook w/non-NEMA Receptacle

INDUSTRIALS—VAPORTIGHT



METAL HALIDE CEILING MOUNT
MHVS-C-GG-70-MT-LL
MHVS-C-GG-100-MT-LL
COMPACT FLUORESCENT CEILING MOUNT
PLVS-C-GG-42-UNV-LL
INCANDESCENT CEILING MOUNT
ICVC1G
ICVC2G
INCANDESCENT PENDANT MOUNT
ICVP1G
ICVP2G
INCANDESCENT WALL MOUNT
ICVW1G
ICVW2G

70W Multi-Tap HPF MH Ceiling w/Lamp
100W Multi-Tap HPF MH Ceiling w/Lamp

42W 120V PL Ceiling w/Lamp

100/200W Ceiling Mount
300W Ceiling Mount

100/200W Pendant Mount
300W Pendant Mount

100/200W Wall Mount
300W Wall Mount

MWS—MODULAR WIRING SYSTEMS



STARTER FITTINGS
12ST12/2G
12ST12/3G
27ST12/2G
27ST12/3G

120V One Hot Neutral and Ground
120V Two Hot Neutral and Ground
277V One Hot Neutral and Ground
277V Two Hot Neutral and Ground