



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IG5261 Recp SGL 15A 125V S+B Wire Ig

Pass & Seymour/Legrand

Catalog Number	IG5261
Manufacturer	Pass & Seymour/Legrand
Description	Isolated Ground Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 125V
Weight per unit	0.1704 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
Material	Nylon
media	Yes
Number of Wires	3
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Color	Orange
-------	--------

Dimensions and Weight

Height	3.68
Width	1.093

Descriptions

Description	RECP SGL 15A 125V S+B WIRE IG
extra long description	P&S IG5261 RECEPT SINGLE 15A 125V S
Long Description	Isolated Ground Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 125V
Product Type	Recept Single 15A 125V S+B Wire Ig
Special Features	IG symbol and Isolated Ground markings for easy identification and circuit delineation. Triple-wipe brass contacts ensure lasting, positive contact with plug blades. High-impact resistant nylon face resists impacts and scrapes. Corrosion-resistant plated steel strap. Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. Plastic barrier isolates grounding terminal from mounting strap and metal boxes. Side and internal screw-pressure-plate back wi



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007652611
Manufacturers Part Number	IG5261
UPC	785007652611

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Isolated Ground Spec Grade Single Receptacle, Heavy-Duty

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.1704

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-15R
standard	CUL, UL498, CSA C22.2 No. 42, FEDSPEC
Temperature Rating	-40° - 60° C