



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IG5362GRY Recep Dup 20A Commer Isol GRD Gry

Pass & Seymour/Legrand

Catalog Number	IG5362GRY
Manufacturer	Pass & Seymour/Legrand
Description	Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and, Side Wire 20AMP 125VOLT Gray
Weight per unit	0.1950 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
Material	Nylon;Other
Number of Wires	3
Poles	2
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Dimensions and Weight

Height	3.281
Width	.922

Descriptions

Description	RECEP DUP 20A COMMER ISOL GRD GRY
extra long description	P&S IG5362GRY RECEP DUP 20A COMMER
Long Description	Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and, Side Wire 20amp 125volt Gray
Product Type	Recep Dup 20A Commer Isol GRD Gry
Special Features	IG symbol and Isolated Ground markings for easy identification and circuit delineation. Triple-wipe brass contacts ensure lasting, positive contact with plug blades. High-impact resistant nylon face resists impacts and scrapes. Corrosion-resistant plated steel strap. Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. Plastic barrier isolates grounding terminal from mounting strap and metal boxes. Side and internal screw-pressure-plate back wi

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007045352
Manufacturers Part Number	IG5362GRY
UPC	785007045352



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Isolated Ground Spec Grade Receptacle, Heavy-Duty

Packaging

Carton	10
Package	100
Weight Per each	0.195

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	UL498, CSA C22.2 No. 42