



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IG8300BLSP Ig TVSS HG Recp 20A 125V Alarm BL

Pass & Seymour/Legrand

Catalog Number	IG8300BLSP
Manufacturer	Pass & Seymour/Legrand
Description	Hospital Grade Isolated Ground Surge Protective Duplex Receptacle Offers Increased Transient Protection, Reliability and Protection Notification (Audible Alarm With Led Indicator). Back and, Side Wire, 20AMP 125VOLT, Blue.
Weight per unit	0.3766 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
class	IG
connection	Back and side wire
Material	Nylon
media	Yes
Number of Wires	3
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10

Material, Color, and Finish

Color	Blue
-------	------

Dimensions and Weight

Height	3.75
Width	1.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	IG TVSS HG RECP 20A 125V ALARM BL
extra long description	P&S IG8300BLSP IG TVSS HG RECP 20A
Long Description	Hospital Grade Isolated Ground Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and, Side Wire, 20amp 125volt, Blue.
Product Type	Ig TVSS HG Recp 20A 125V Alarm BL
Special Features	IG symbol and Isolated Ground markings for easy identification and circuit delineation. Plastic barrier isolates grounding terminal from mounting strap and metal boxes. Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place. LED Indication: steady green = protected, flashing red = not protected, OFF = no power to unit. Audible alarm alert of MOV damage. Alarm able to be turned On/Off. Wrap-around steel strap for structural integrity.

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007194623
Manufacturers Part Number	IG8300BLSP
UPC	785007194623

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Isolated Ground Hospital Grade Surge Protective Receptacle, Audible Alarm with LED Indicator

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.3766



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	CULUS, cUL UL1449, UL498: CSA C22.2 No. 42: ANSI/EEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).
Temperature Rating	Operating Temperature: -20°C to +55°C (-4°F to 131°F), Storage Temperature: -40°C to +85°C (-40°F to 185°F)