



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IMH100DBLS 120-277V Elec Bal

*Advance By Signify*

Catalog Number	IMH100DBLS
Manufacturer	Advance By Signify
Description	Ballast, Metal Halide, Lamp Type: MH, Ballast Type: Electronic Hid, Voltage: 120-277, Wattage: 100, BLFS
Weight per unit	1.5 (lbs/each)
Product Category	Electronic Hid Ballasts

### Features

ANSI Code	M140
Ballast Type	Electronic HID
Circuit Type	LOW FREQUENCY
Lamp Type	MH
Number of Lamps	1 PH
Output Type	FIXED
start type	PULSE START
Voltage Rating	277 VAC
Wattage	100 WTT

### Descriptions

Description	120-277V ELEC BAL
extra long description	ADV IMH100DBLSM ELE MH BAL 100W M14
Long Description	Ballast, Metal Halide, Lamp Type: MH, Ballast Type: Electronic HID, Voltage: 120-277, Wattage: 100, BLFS
Product Type	Ele MH Bal 100W M140 120-277V 50/60HZ

### Manufacturer Information

Brand	Signify Electronics
GTIN	00781087032213
Manufacturers Part Number	IMH100DBLSM
sub brand	E-VISION
UPC	781087032213

### Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
----------------------	--------------------

### Availability

Manufacturer Status	Inactive
Status	Inactive

### Packaging

Carton	1
Package	10
Weight Per each	1.5