

IEC Pin and Sleeve Watertight Devices Plug/Inlet Replacement Interior

HUBBELL

Features

- Thermoset Polyester Contact Carrier

Ordering Information

Description Pin and Sleeve Replacement Interior, For 3W 20A, IEC	UPC 783585420035	Catalog Number IN320BM
---	----------------------------	---

Device Color
Black



Standards

UL Listed
CSA Certified

Specifications

Gaskets	Neoprene
Hinge Spring	Stainless Steel
Contact Carrier	High-Impact Thermoset
Retainer	High-Impact Thermoset
Terminal Screws	Stainless Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 3,000V AC
Max Working Voltage 600V AC RMS

Mechanical

Impact Resistance In accordance with UL746C
Product Identification Identification and ratings are a part of the external label and molded into the receptacle mount
Terminal Identification Terminals identified in accordance with North American and International conventions

Environmental

Flammability UL94-5VA and V-0 classification
Ingress Protection IP67 Suitability
Operating Temperatures Max. Continuous:75°C; Min. Continuous:-40°C w/o impact

Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

