



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IPL43C 4-14AWG 3PRT Insld Tap Conn

Nsi Industries

Catalog Number	IPL43C
Manufacturer	Nsi Industries
Description	The Polaris IPL4-3C Multi-Tap Single Side Entry Vision Tap Connector Features 3 Ports Sized For 4 - 14 Awg Wires. The Clear Body Allows Users to See Their Conductor Placement and Is Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including In
Weight per unit	0.0800 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Aluminum
Number of Conductors	3
Poles	1
Voltage Rating	600
Warranty	1 YEAR
Wire Size	4-14 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Clear
Finish	Plastisol Insulated

Dimensions and Weight

Size	L=1.550 - W=1.188 - H=1.375
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	4-14AWG 3PRT INSLTD TAP CONN
extra long description	NSI IPL4-3C POLARIS Vision Tap 4 3
Features	The Polaris IPL4-3C 3-Port Single-Side Connector provides the simplest solution for forming a secure connection between up to three conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 4 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The clear body lets installers see their work for optimal condu
Long Description	The Polaris IPL4-3C Multi-Tap Single Side Entry Vision Tap Connector features 3 ports sized for 4 - 14 AWG wires. The clear body allows users to see their conductor placement and is wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including in
Product Type	Polaris Vision Tap 4 3 Port Sse
Special Features	(3) 4-14 AWG - Dual Rated

Manufacturer Information

Brand	Polaris
GTIN	00662381996442
Manufacturers Part Number	IPL4-3C
UPC	662381996442

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Single Sided Entry

Packaging

Carton	12
Weight Per each	0.08

Uses, Certifications, and Standards

Application	Wire Termination
Enclosure	Clear Plastisol
environmental conditions	Dry Location Only
standard	UL 486A/B
Temperature Rating	90