



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IPLD50012 500MCM 12port

*Nsi Industries*

Catalog Number	IPLD50012
Manufacturer	Nsi Industries
Description	The Polaris IPLD500-12 Multi-Tap Dual-Sided Entry Connector Features 12 Ports Sized For 500 MCM - 4 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Tra
Weight per unit	3.1 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Number of Conductors	12
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	500 MCM-4 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=14.400 - W=2.830 - H=2.910
------	------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	500MCM 12PORT
extra long description	NSI IPLD500-12 POLARIS Ins Multi-Ta
Features	The Polaris IPLD500-12 12-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to twelve conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 500 MCM - 4 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric
Long Description	The Polaris IPLD500-12 Multi-Tap Dual-Sided Entry Connector features 12 ports sized for 500 MCM - 4 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable tra
Product Type	Polaris Ins Multi-Tap 500 12 Port Dse
Special Features	(12) 500 MCM-4 AWG - Dual Rated

## Manufacturer Information

Brand	NSi
GTIN	00662381925107
Manufacturers Part Number	IPLD500-12
UPC	662381925107

## Taxonomies, Classifications, and Categories

Type	Double Sided Entry
------	--------------------

## Packaging

Carton	1
Weight Per each	3.13

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C