



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IPLMD35012 350MCM-10AWG 12PRT 2SIDE Multi-Tap Conn

*Nsi Industries*

Catalog Number	IPLMD35012
Manufacturer	Nsi Industries
Description	The Polaris IPLMD350-12 Multi-Tap Mountable Dual-Sided Entry Connector Features 12 Ports Sized For 350 MCM - 6 Awg Wires. Mounting Holes On Either Side Of The Connector Allow For Direct Mounting to Troughs, Panels or Wireways With 1/4" Bolts. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Wi
Weight per unit	2.6 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Number of Conductors	12
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	350 MCM-6 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=14.570 - W=2.410 - H=2.770
------	------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	350MCM-10AWG 12PRT 2SIDE MULTI-TAP CONN
extra long description	NSI IPLMD350-12 POLARIS Mount Ins M
Features	The Polaris IPLMD350-12 12-Port Dual-Sided Mountable Connector provides the simplest solution for forming a secure connection between up to twelve conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 350 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. Mountable connectors feature 1/4" mounting
Long Description	The Polaris IPLMD350-12 Multi-Tap Mountable Dual-Sided Entry Connector features 12 ports sized for 350 MCM - 6 AWG wires. Mounting holes on either side of the connector allow for direct mounting to troughs, panels or wireways with 1/4" bolts. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, wi
Product Type	Polaris Mount Ins Multi-Tap 350 12 Port
Special Features	(12) 350 MCM-6 AWG - Dual Rated - With Mounting Holes

## Manufacturer Information

Brand	NSi
GTIN	00662381944108
Manufacturers Part Number	IPLMD350-12
UPC	662381944108

## Taxonomies, Classifications, and Categories

Type	Double Sided Entry With Mounting Holes
------	--

## Packaging

Carton	1
Weight Per each	2.58

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C