



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IR07 Dual Ir/Probe Thermometer

*Klein Tools*

Catalog Number	IR07
Manufacturer	Klein Tools
Description	The Klein Tools IR07 Is A Dual Ir (Infrared) Thermometer and Probe Thermometer. This Rugged Pocket Thermometer Measures Temperature From -40 to 572-Degrees Fahrenheit (-40 to 400-Degrees Celsius) For Both Ir and Probe Measurements. The Ir Thermometer Has A Distance-to-Spot Ratio Of 8:1 and The Target Laser Can Also Be Used As A Laser Pointer. The Probe Accurately Measures Air, Liquid and Surface Temps and Has A Convenient Hook For Hands Free Indoor Measurements. The IR07 Quickly Calculates Differential Tem
Weight per unit	0.0870 (lbs/each)
Product Category	Meters, Panel Instruments

### Features

Accuracy	-40 to 0° C: +/-2°; 1 to 300° C: +/- 1°C
display	Backlit LCD
included	IR07 Dual IR and Probe Thermometer; Pouch; Owner's Manual and 2 x AAA Batteries
Material	ABS, Polycarbonate
media	Yes
Overall Height	0.95" (2.4 cm)
Overall Width	1.67" (4.2 cm)
Range	-40° to 572° F (-40° to 300° C)
Response Time	IR <500 ms; Probe <20 s

### Dimensions and Weight

Overall Length	5.82" (14.8 cm)
----------------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	DUAL IR/PROBE THERMOMETER
extra long description	KLEIN IR07 Dual IR/Probe Digital T
Features	The Klein Tools IR07 is a dual IR (infrared) thermometer and probe thermometer. This rugged pocket thermometer measures temperature from -40 to 572-Degrees Fahrenheit (-40 to 400-Degrees Celsius) for both IR and probe measurements. The IR thermometer has a Distance-to-Spot ratio of 8:1 and the target laser can also be used as a laser pointer. The Probe accurately measures air, liquid and surface temps and has a convenient hook for hands free indoor measurements. The IR07 quickly calculates differential tem
Long Description	The Klein Tools IR07 is a dual IR (infrared) thermometer and probe thermometer. This rugged pocket thermometer measures temperature from -40 to 572-Degrees Fahrenheit (-40 to 400-Degrees Celsius) for both IR and probe measurements. The IR thermometer has a Distance-to-Spot ratio of 8:1 and the target laser can also be used as a laser pointer. The Probe accurately measures air, liquid and surface temps and has a convenient hook for hands free indoor measurements. The IR07 quickly calculates differential tem
Product Type	Dual Ir/Probe Digital Thermometer
Special Features	Pocket Sized, IR and Probe Thermometer; Hanging Hook for Use with Air Vents

## Manufacturer Information

Brand	Klein Tools
GTIN	00092644691812
Manufacturers Part Number	IR07
UPC	092644691812

## Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	Pocket Infrared Thermometer with Laser and Temperature Probe

## Packaging

Carton	1
Package	4
Weight	3.60 oz (106.5 g)
Weight Per each	0.087

## Uses, Certifications, and Standards

Application	Temperature Measurement via IR (Infrared) and Probe
standard	IEC EN 61326-1:2013; EN61326-2-3:2013