ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



ISPB202 14-2/0AWG CONN

NSI INDUSTRIES

Catalog Number	ISPB202
Manufacturer	NSI INDUSTRIES
Description	The Polaris ISPB2/0-2 Multi-Tap Direct Burial Single-Sided Entry Connector features 2 ports sized for 2/0 - 14 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each single-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Rated for temporary submersion, wet or damp locations and direct burial applications. Installs with a hex key and torque wrench, w
Weight per unit	0.2000 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Number Of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	2/0-14 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	EPDM Rubber Insulated

Dimensions and Weight

Size	L=1.93 - W=2.65 - H=2.10

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Descriptions

Description	14-2/0AWG CONN
Features	The Polaris ISPB2/0-2 2-Port Single-Sided Submersible Connector provides the simplest solution for forming a secure connection between two conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 2/0 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielec
Long Description	The Polaris ISPB2/0-2 Multi-Tap Direct Burial Single-Sided Entry Connector features 2 ports sized for 2/0 - 14 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each single-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Rated for temporary submersion, wet or damp locations and direct burial applications. Installs with a hex key and torque wrench, w
Product Type	Polaris Edge DB Connector 2/0-14 2 Port
Special Features	(2) 2/0-14 AWG - Dual Rated
Extra Long Description	NSI ISPB2/0-2 Polaris Edge DB Conne

Manufacturer Information

Brand	Nsi Industries
GTIN	00662381787835
Manufacturers Part Number	ISPB2/0-2
UPC	884739

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Submersible Pedestal Connectors

Packaging

Carton	3
Weight Per Each	0.2000 (lbs/each)

Uses, Certifications, and Standards

Application	Wire Termination
Temperature Rating	90 C
Environmental Conditions	90 C
Standard	ANSI C119.4, C119.1, UL486D