



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ISPB202 14-2/0AWG Conn

Nsi Industries

Catalog Number	ISPB202
Manufacturer	Nsi Industries
Description	The Polaris ISPB2/0-2 Multi-Tap Direct Burial Single-Sided Entry Connector Features 2 Ports Sized For 2/0 - 14 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of High-Dielectric Strength Rubber Insulation. Each Single-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Radial-Tipped Set Screws. Rated For Temporary Submersion, Wet or Damp Locations and Direct Burial Applications. Installs With A Hex Key and Torque Wrench, W
Weight per unit	0.2000 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	2/0-14 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	EPDM Rubber Insulated

Dimensions and Weight

Size	L=1.93 - W=2.65 - H=2.10
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	14-2/0AWG CONN
extra long description	NSI ISPB2/0-2 POLARIS EDGE Connecto
Features	The Polaris ISPB2/0-2 2-Port Single-Sided Submersible Connector provides the simplest solution for forming a secure connection between two conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 2/0 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielec
Long Description	The Polaris ISPB2/0-2 Multi-Tap Direct Burial Single-Sided Entry Connector features 2 ports sized for 2/0 - 14 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each single-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Rated for temporary submersion, wet or damp locations and direct burial applications. Installs with a hex key and torque wrench, w
Product Type	Polaris Edge Connector 2/0 2 Port Epdm
Special Features	(2) 2/0-14 AWG - Dual Rated

Manufacturer Information

Brand	Polaris
GTIN	00662381787835
Manufacturers Part Number	ISPB2/0-2
UPC	662381787835

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Submersible Pedestal Connectors

Packaging

Carton	3
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	ANSI C119.4, C119.1, UL486D
Temperature Rating	90 C