



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ISPB203B 2/0-14AWG 3PRT Submerge PDSTL Conn

*Nsi Industries*

Catalog Number	ISPB203B
Manufacturer	Nsi Industries
Description	The Polaris ISPB2/0-3B Multi-Tap Direct Burial Single-Sided Entry Connector Features 3 Ports Sized For 2/0 - 14 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of High-Dielectric Strength Rubber Insulation. Each Single-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Radial-Tipped Set Screws. Rated For Temporary Submersion, Wet or Damp Locations and Direct Burial Applications. Installs With A Hex Key and Torque Wrench,
Weight per unit	0.3000 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Number of Conductors	3
Poles	1
Voltage Rating	600
Warranty	1 YEAR
Wire Size	2/0-14 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	EPDM Rubber Insulated

### Dimensions and Weight

Size	L=2.79 - W=2.65 - H=2.10
------	--------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	2/0-14AWG 3PRT SUBMERSE PDSTL CONN
extra long description	NSI ISPB2/0-3B POLARIS EDGE Conn 2/
Features	The Polaris ISPB2/0-3B 3-Port Single-Sided Submersible Connector provides the simplest solution for forming a secure connection between up to three conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 2/0 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in hi
Long Description	The Polaris ISPB2/0-3B Multi-Tap Direct Burial Single-Sided Entry Connector features 3 ports sized for 2/0 - 14 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each single-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Rated for temporary submersion, wet or damp locations and direct burial applications. Installs with a hex key and torque wrench,
Product Type	Polaris Edge Conn 2/0 3 Port Epdm Bag
Special Features	(3) 2/0-14 AWG - Bagged - Dual Rated

## Manufacturer Information

Brand	NSi
GTIN	00662381800619
Manufacturers Part Number	ISPB2/0-3B
UPC	662381800619

## Taxonomies, Classifications, and Categories

Type	Submersible Pedestal Connectors
------	---------------------------------

## Packaging

Carton	1
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90
standard	ANSI C119.4, C119.1, UL486D
Temperature Rating	90