



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ISPB3504 350MCM-12AWG 4PRT Ped Conn

Nsi Industries

| | |
|------------------|---|
| Catalog Number | ISPB3504 |
| Manufacturer | Nsi Industries |
| Description | The Polaris ISPB350-4 Multi-Tap Direct Burial Single-Sided Entry Connector Features 4 Ports Sized For 350 MCM - 12 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of High-Dielectric Strength Rubber Insulation. Each Single-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Radial-Tipped Set Screws. Rated For Temporary Submersion, Wet or Damp Locations and Direct Burial Applications. Installs With A Hex Key and Torque Wrenc |
| Weight per unit | 0.7300 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|----------------|
| Material | Aluminum |
| Number of Conductors | 4 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 350 MCM-12 AWG |
| Wire Type | Class B & C |

Material, Color, and Finish

| | |
|--------|-----------------------|
| Color | Black |
| Finish | EPDM Rubber Insulated |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=4.800 - W=4.190 - H=3.060 |
|------|-----------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | 350MCM-12AWG 4PRT PED CONN |
| extra long description | NSI ISPB350-4 POLARIS EDGE Connector |
| Features | The Polaris ISPB350-4 4-Port Single-Sided Submersible Connector provides the simplest solution for forming a secure connection between up to four conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 350 MCM - 12 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in |
| Long Description | The Polaris ISPB350-4 Multi-Tap Direct Burial Single-Sided Entry Connector features 4 ports sized for 350 MCM - 12 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each single-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Rated for temporary submersion, wet or damp locations and direct burial applications. Installs with a hex key and torque wrench |
| Product Type | Polaris Edge Connector 350 4 Port BLK |
| Special Features | (4) 350 MCM-12 AWG - Dual Rated |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Polaris |
| GTIN | 00662381788962 |
| Manufacturers Part Number | ISPB350-4 |
| UPC | 662381788962 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------------|
| Category Description | TERMINALS |
| Type | Submersible Pedestal Connectors |

Packaging

| | |
|-----------------|------|
| Carton | 2 |
| Weight Per each | 0.73 |

Uses, Certifications, and Standards

| | |
|--------------------------|---------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | ANSI C119.4, C119.1 |
| Temperature Rating | 90 C |