



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ISR10 1/0 Polaris Insulated Butt SPLC

Nsi Industries

| | |
|------------------|--|
| Catalog Number | ISR10 |
| Manufacturer | Nsi Industries |
| Description | Insulated Butt Splice, #14 Awg Conductor Size, #1/0 Awg Conductor Size, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, -45 °C (Cold) Operating Temperature, +90 °C Operating Temperature, 3.25 In Overall Length, 600 V, 0.15 LB |
| Weight per unit | 0.1500 (lbs/each) |
| Product Category | Splicing & Terminating Kits |

Features

| | |
|----------------------|-------------|
| Material | Aluminum |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 1/0-14 AWG |
| Wire Type | Class B & C |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Black |
| Finish | Plastisol Insulated |

Dimensions and Weight

| | |
|------|----------------------------|
| Size | L=3.250 - W=.900 - H=1.480 |
|------|----------------------------|

Descriptions

| | |
|------------------------|------------------------------------|
| Description | 1/0 POLARIS INSULATED BUTT SPLC |
| extra long description | NSI ISR-1/0 POLARIS Ins Splice 1/0 |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00662381951014 |
| UPC | 662381951014 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | SPLIT BOLTS |
| Type | IN-Line Splicer/Reducer |

Packaging

| | |
|-----------------|------|
| Carton | 4 |
| Weight Per each | 0.15 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | UL 486A/B |
| Temperature Rating | 90 C |