Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ISR500 500MCM Polaris Insulated Butt SPLC

Nsi Industries

Catalog Number	ISR500
Manufacturer	Nsi Industries
Description	Insulated Butt Splice, #4 Awg Conductor Size, 500 MCM Conductor Size, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, -45 °C (Cold) Operating Temperature, +90 °C Operating Temperature, 4.62 In Overall Length, 600 V, 0.72 LB
Weight per unit	0.7200 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	500 MCM-4 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated
Housing Material	Aluminum

Dimensions and Weight

Size	L=4.620 - W=1.620 - H=3.000

Descriptions

Description	500MCM POLARIS INSULATED BUTT SPLC
extra long description	NSI ISR-500 500 Mcm - 4 Awg Polaris

Manufacturer Information

GTIN	00662381951045
UPC	662381951045

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	IN-Line Splicer/Reducer

Packaging

Carton	2
Weight Per each	0.72

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B