



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ISR600 Polaris Conn. 600-6 *Nsi Industries*

Catalog Number	ISR600
Manufacturer	Nsi Industries
Description	Insulated Butt Splice, #6 Awg Conductor Size, 600 Kcmil Conductor Size, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, -45 °C (Cold) Operating Temperature, +90 °C Operating Temperature, 5.83 In Overall Length, 600 V, 1 LB
Weight per unit	1.0 (lbs/each)
Product Category	Splicing & Terminating Kits

### Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	600 MCM-6 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=5.830 - W=1.570 - H=3.050
------	-----------------------------

### Descriptions

Description	POLARIS CONN. 600-6
extra long description	NSI ISR-600 POLARIS Ins Splice 600

### Manufacturer Information

GTIN	00662381789457
UPC	662381789457

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	IN-Line Splicer/Reducer

### Packaging

Carton	2
Weight Per each	1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	75 C
standard	UL 486A/B
Temperature Rating	75 C