



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IT030B 3/0-6 Awg Insulated Tap Connector, Off-Set (Dual)

Nsi Industries

Catalog Number	IT030B
Manufacturer	Nsi Industries
Description	The Polaris Ito-3/0B Multi-Tap Offset Dual-Side Entry Connector Features 2 Ports Sized For 3/0 - 6 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Trays, Panel Bo
Weight per unit	0.1900 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	3/0-6 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

Dimensions and Weight

Size	L=1.840 - W=1.870 - H=1.870
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	3/0-6 AWG INSULATED TAP CONNECTOR, OFF-SET (DUAL
extra long description	NSI ITO-3/0B POLARIS Multi Tap 3/0
Features	The Polaris ITO-3/0B 2-Port Offset Dual-Sided Connector provides the simplest solution for forming a secure connection between two conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 3/0 - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strength
Long Description	The Polaris ITO-3/0B Multi-Tap Offset Dual-Side Entry Connector features 2 ports sized for 3/0 - 6 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable trays, panel bo
Product Type	Polaris Multi Tap 3/0 2 Port Offset Bag
Special Features	(2) 3/0-6 AWG - Dual Rated - Offset Ports - 1 Pcs Per Pack

Manufacturer Information

Brand	NSi
GTIN	00662381953094
Manufacturers Part Number	ITO-3/0B
UPC	662381953094

Taxonomies, Classifications, and Categories

Category Description	T&B C TAP LUGS
Type	Multi Cable

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	0.19

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C