



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



J2078CR All-Purpose Needle Nose Pliers W/ Crimper, 8.5"

Klein Tools

Catalog Number	J2078CR
Manufacturer	Klein Tools
Description	All-Purpose Pliers With Crimper, Steel Blade Material, 1/2 In Blade Length, Black;Yellow (Handle), Journeyman (Handle), 8-5/8 In Overall Length, 2-3/16 In Jaw Length, 1 In Jaw Width, 9.6 Oz
Weight per unit	0.6000 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Length	4.55" (11.6 cm)
Handle Type	Soft Touch Grip
jaw thickness	0.5
knife length	0.5" (1.3 cm)
Material	Steel
Point Diameter	0.15" (0.38 cm)
tether capable	No

Material, Color, and Finish

Handle Color	YELLOW/BLACK
--------------	--------------

Descriptions

Description	ALL-PURPOSE NEEDLE NOSE PLIERS W/ CRIMPER, 8.5"
extra long description	KLEIN J207-8CR All-Purpose Pliers w
Special Features	Includes Crimper

Manufacturer Information

GTIN	00092644384059
Manufacturers Part Number	J207-8CR
UPC	092644384059

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	All-Purpose Pliers - Crimping

Packaging

Carton	1
Package	6
Weight Per each	0.6

Uses, Certifications, and Standards

Application	8-16 AWG Solid and 10-18 AWG Stranded Wire
-------------	--