



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



K2C22B1 3STR Split Bolt Conn

Burndy LLC

Catalog Number	K2C22B1
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, 2 Cables to Flat, 10 - 3 Awg (STR) / 10 - 2 Awg (Sol).
Weight per unit	0.1300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Bronze Alloy, Leaded
pallet quantity	14850

Descriptions

Description	3STR SPLIT BOLT CONN
extra long description	BUR K2C22B1 10-3 STR 31/32 POST 2 C
Long Description	Mechanical Grounding Connector, 2 Cables to Flat, 10 - 3 AWG (Str) / 10 - 2 AWG (Sol).
Product Type	Mechanical
Special Features	Features: SERVIT POST Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar, One-Wrench Installation, Conductor Type: Run: Commercial Stranded Copper, Commercial Solid Copper, Cross Flats: 3/4, 5/8 IN, Height: 2-3/8 IN, Dimension B: 31/32 IN, Stud Size: 3/8-16

Manufacturer Information

Brand	BURNDY
GTIN	00781810257159
Manufacturers Part Number	K2C22B1
UPC	781810257159

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KC and K2C Series

Packaging

Carton	1
Weight Per each	0.13

Uses, Certifications, and Standards

Application	For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial
standard	UL467