

**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

KA25U  
 7818103701933  
 14STR-1/0STR DUAL RATED  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Width (in) 0.63  
 Length (in) 1.50  
 Bolt Hole Size (in) 0.25  
 Thickness 0.19  
 D - in 0.81  
 Pad Width (in) 0.63  
 N (in) 0.44

**General**

Number of Conductors 1  
 Number of Holes 1  
 Product Description Aluminum Universal Terminal, 1 Hole, 14-1/0 AWG (Str), 1/4" Stud, 1 Screw, Al/Cu Rated, Tin Plated

**Conductor(s)**

Aluminum Size (Range) 14 STR- 1/0 STR  
 Copper Solid Size (Range) 12 AWG-1/0 AWG  
 Copper Stranded (Range) 14 AWG-1/0

**Physical**

Installation Torque 50  
 Type of Plating Tin  
 Connector Type Terminal  
 Bolt Hole Size 1/4  
 Plated (Yes or No) Y  
 Product Material Aluminum

**Approvals / Certifications**

Rated for Direct Burial N  
 UL Listed Y  
 CSA Certified Y  
 ROHS Compatible Exempt  
 Industry Standards UL468A-468B

**Documentation**

For further technical assistance, please contact us


**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

KA25U  
 7818103701933  
 14STR-1/0STR DUAL RATED  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Width (in)	0.63
Length (in)	1.50
Bolt Hole Size (in)	0.25
Thickness	0.19
D - in	0.81
Pad Width (in)	0.63
N (in)	0.44

**General**

Number of Conductors	1
Number of Holes	1
Product Description	Aluminum Universal Terminal, 1 Hole, 14-1/0 AWG (Str), 1/4" Stud, 1 Screw, Al/Cu Rated, Tin Plated

**Conductor(s)**

Aluminum Size (Range)	14 STR- 1/0 STR
Copper Solid Size (Range)	12 AWG-1/0 AWG
Copper Stranded (Range)	14 AWG-1/0

**Physical**

Installation Torque	50
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	1/4
Plated (Yes or No)	Y
Product Material	Aluminum

**Approvals / Certifications**

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175