

BURNDY Catalog Number
UPC Number
Description
Status

KA29U
 7818103701555
 6STR-250 DUAL RATED
 Active

Web Use
 BURNDY Product Line

Dimensional	
Width (in)	1.00
Length (in)	2.00
Bolt Hole Size (in)	0.31
Thickness	0.25
D - in	0.94
Pad Width (in)	1.02
N (in)	0.47
General	
Number of Conductors	1
Number of Holes	1
Product Description	Aluminum Universal Terminal, 1 Hole, 6 AWG (Str)-250 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated, Tin Plated
Conductor(s)	
Aluminum Size (Range)	6 STR- 250 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	6-250
Physical	
Installation Torque	275
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	5/16
Plated (Yes or No)	Y
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us



BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175



BURNDY Catalog Number
UPC Number
Description
Status

KA29U
 7818103701555
 6STR-250 DUAL RATED
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 1.00
 Length (in) 2.00
 Bolt Hole Size (in) 0.31
 Thickness 0.25
 D - in 0.94
 Pad Width (in) 1.02
 N (in) 0.47

General

Number of Conductors 1
 Number of Holes 1
 Product Description Aluminum Universal Terminal, 1 Hole, 6 AWG (Str)-250 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range) 6 STR- 250 kcmil
 Copper Solid Size (Range) N/A
 Copper Stranded (Range) 6-250

Physical

Installation Torque 275
 Type of Plating Tin
 Connector Type Terminal
 Bolt Hole Size 5/16
 Plated (Yes or No) Y
 Product Material Aluminum

Approvals / Certifications

Rated for Direct Burial N
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Exempt
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175