

Specifications



Eaton KLM-20

Eaton Bussmann series KLM fuse, 20 A, Non-indicating, Ferrule end x ferrule end, 100 kAIC at 600 V, 50 kAIC at 600 Vdc, Melamine tube, Nickel-plated bronze endcap, 600 V, 600 Vdc

General specifications

PRODUCT NAME	Eaton Bussmann series KLM fuse
CATALOG NUMBER	KLM-20
UPC	051712695206
PRODUCT LENGTH/DEPTH	0.001 in
PRODUCT HEIGHT	0.001 in
PRODUCT WIDTH	0.001 in
PRODUCT WEIGHT	0.18 lb
WARRANTY	Not Applicable
COMPLIANCES	RoHS Compliant CE Marked



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	20 A
INTERRUPT RATING	100 kAIC at 600 Vac 50 kAIC at 600 Vdc
VOLTAGE RATING	600 Vac, 600 Vdc

General information

CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
SPECIAL FEATURES	Non-indicating

Physical details

MATERIAL	Nickel-plated bronze endcap Melamine tube
PACKAGING TYPE	Standard

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - KLM-20
TECHNICAL DATA SHEETS	KLM-20~LIMITRON FAST ACTING FUSE
TECHNICAL SERVICE BULLETINS	Datasheet - FNQ-30

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

