



BURNDY Catalog Number
UPC Number
Description
Status

KS15
 7818100112566
 CU SB 10 STR - 8 STR
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 0.38
 Cross Flats 0.50
 B Length (in) .45
 B Length (Fraction) 9/20

General

Product Description

Copper Split Bolt, Cu: 10-8 AWG
 (Str) (Run & Tap)

Conductor(s)

Copper Tap Range 14 AWG-8 AWG
 CopperWeld Solid Run Size (Range) 20 AWG
 Copper Stranded Run (Range) 10 AWG-8 AWG
 CopperWeld Stranded Tap Size (Range) N/A
 Copper Solid Tap (Range) 14 AWG-8 AWG
 CopperWeld Solid Tap Size (Range) #8
 Copper Solid Run Size (Range) 10 AWG-8 AWG
 CopperWeld Stranded Run Size (Range) 9 D AWG

Physical

Installation Torque 80
 Type of Plating Unplated
 Connector Type Split Bolt
 Plated (Yes or No) N
 Product Material Copper

Approvals / Certifications

Rated for Direct Burial Y
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL467,UL486,CSA C22.2 No 41

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175



BURNDY Catalog Number
UPC Number
Description
Status

KS15
 7818100112566
 CU SB 10 STR - 8 STR
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 0.38
 Cross Flats 0.50
 B Length (in) .45
 B Length (Fraction) 9/20

General

Product Description Copper Split Bolt, Cu: 10-8 AWG (Str) (Run & Tap)

Conductor(s)

Copper Tap Range 14 AWG-8 AWG
 CopperWeld Solid Run Size (Range) 20 AWG
 Copper Stranded Run (Range) 10 AWG-8 AWG
 CopperWeld Stranded Tap Size (Range) N/A
 Copper Solid Tap (Range) 14 AWG-8 AWG
 CopperWeld Solid Tap Size (Range) #8
 Copper Solid Run Size (Range) 10 AWG-8 AWG
 CopperWeld Stranded Run Size (Range) 9 D AWG

Physical

Installation Torque 80
 Type of Plating Unplated
 Connector Type Split Bolt
 Plated (Yes or No) N
 Product Material Copper

Approvals / Certifications

Rated for Direct Burial Y
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL467,UL486,CSA C22.2 No 41

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175