



BURNDY Catalog Number
UPC Number
Description
Status

KS17
 7818100115088
 SERVIT 8STR - 6SOL
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 0.45
 Size (Hex) or Size (Bolt) 7/16
 Cross Flats 0.63
 Size (Hex) or Size (Bolt) - in 0.438
 B Length (in) .58
 B Length (Fraction) 29/50

General

Product Description

Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap),Length:1.14

Conductor(s)

Copper Tap Range 14 AWG-6 AWG
 CopperWeld Solid Run Size (Range) 6 AWG
 Copper Stranded Run (Range) 8 AWG-6 AWG
 CopperWeld Stranded Tap Size (Range) 9-1/2 D-3#12
 Copper Solid Tap (Range) 14 AWG-6 AWG
 CopperWeld Solid Tap Size (Range) 6 AWG
 Copper Solid Run Size (Range) 8 AWG-6 AWG
 CopperWeld Stranded Run Size (Range) 9-1/2D -3#12

Physical

Installation Torque 165
 Type of Plating Unplated
 Connector Type Split Bolt
 Plated (Yes or No) N
 Product Material Copper

Approvals / Certifications

Rated for Direct Burial Y
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards RUS

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175



BURNDY Catalog Number
UPC Number
Description
Status

KS17
 7818100115088
 SERVIT 8STR - 6SOL
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 0.45
 Size (Hex) or Size (Bolt) 7/16
 Cross Flats 0.63
 Size (Hex) or Size (Bolt) - in 0.438
 B Length (in) .58
 B Length (Fraction) 29/50

General

Product Description

Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap),Length:1.14

Conductor(s)

Copper Tap Range 14 AWG-6 AWG
 CopperWeld Solid Run Size (Range) 6 AWG
 Copper Stranded Run (Range) 8 AWG-6 AWG
 CopperWeld Stranded Tap Size (Range) 9-1/2 D-3#12
 Copper Solid Tap (Range) 14 AWG-6 AWG
 CopperWeld Solid Tap Size (Range) 6 AWG
 Copper Solid Run Size (Range) 8 AWG-6 AWG
 CopperWeld Stranded Run Size (Range) 9-1/2D -3#12

Physical

Installation Torque 165
 Type of Plating Unplated
 Connector Type Split Bolt
 Plated (Yes or No) N
 Product Material Copper

Approvals / Certifications

Rated for Direct Burial Y
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards RUS

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175