



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KS26 Servit 2 STR - 2/0 STR Cu Burndy LLC

Catalog Number	KS26
Manufacturer	Burndy LLC
Description	Copper Split Bolt, Cu: 2 Awg-2/0 Awg (STR) (Run & Tap).
Weight per unit	0.2400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
pallet quantity	8700

Descriptions

Description	SERVIT 2 STR - 2/0 STR CU
extra long description	BUR KS26 SERVIT 2 STR-2/0 STR CU
Long Description	Copper Split Bolt, Cu: 2 AWG-2/0 AWG (Str) (Run & Tap).
Product Type	Mechanical
Special Features	Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, Compact, High-Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Cracking And Corrosion, Conductor Type: Run And Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Stranded Copperweld, Installation Torque: 385 IN-LB, Length: 1.94 IN, Cross Flats: 15 IN, Width: 0.82 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810013281
Manufacturers Part Number	KS26
UPC	781810013281

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KS, Compact

Packaging

Carton	1
Package	25
Weight Per each	0.24

Uses, Certifications, and Standards

Application	For Direct Burial Applications In Earth Or Concrete, Copper
standard	UL 486A;UL486B