



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KS29 Servit 1 STR - 250 *Burndy LLC*

Catalog Number	KS29
Manufacturer	Burndy LLC
Description	Copper Split Bolt, Cu: 1 Awg (STR)-250 Kcmil (Run & Tap).
Weight per unit	0.4100 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
pallet quantity	4625

Descriptions

Description	SERVIT 1 STR - 250
extra long description	BUR KS29 SERVIT 1 STR - 250
Long Description	Copper Split Bolt, Cu: 1 AWG (Str)-250 kcmil (Run & Tap).
Product Type	Mechanical
Special Features	Features: Compact, High Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Season Cracking And Corrosion, The SERVIT Provides Maximum Pressure And Assures A Secure Connection On All Combinations Of Run And Tap Conductors, Conductor Type: Run: Solid Copperweld, Commercial Stranded And Solid Copper, Stranded Copperweld, Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Stranded Copperweld, Installation Torque: 650 IN-LB, Cross

Manufacturer Information

Brand	BURNDY
GTIN	00781810013809
Manufacturers Part Number	KS29
UPC	781810013809

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KS

Packaging

Carton	25
Weight Per each	0.41

Uses, Certifications, and Standards

Application	For Direct Burial Cables
standard	UL 486A;UL486B