



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## KS44 1000MCM Split Bolt Conn

*Burndy LLC*

Catalog Number	KS44
Manufacturer	Burndy LLC
Description	Copper Split Bolt, Cu: 300-1000 Kcmil (Run & Tap).
Weight per unit	2.3 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
----------	--------

### Descriptions

Description	1000MCM SPLIT BOLT CONN
extra long description	BUR KS44 SERVIT 300 - 1000
Long Description	Copper Split Bolt, Cu: 300-1000 kcmil (Run & Tap).
Product Type	Mechanical
Special Features	Features: Compact, High Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Season Cracking And Corrosion, The SERVIT Provides Maximum Pressure And Assures A Secure Connection On All Combinations Of Run And Tap Conductors, Conductor Type: Run: Commercial Stranded And Solid Copper, Tap: Commercial Stranded And Solid Copper, Installation Torque: 1100 IN-LB, Length: 3.73 IN, Cross Flats: 2.56 IN, Width: 2.19 IN

### Manufacturer Information

Brand	BURNDY
GTIN	00781810015001
Manufacturers Part Number	KS44
UPC	781810015001

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KS

### Packaging

Carton	1
Weight Per each	2.31

### Uses, Certifications, and Standards

Application	For Direct Burial Cables
standard	UL 486A;UL486B