



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KS90 10SOL Split Bolt Conn

Burndy LLC

Catalog Number	KS90
Manufacturer	Burndy LLC
Description	Copper Split Bolt, Cu: 12-10 Awg (STR) (Run & Tap).
Weight per unit	0.0260 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
pallet quantity	99000

Descriptions

Description	10SOL SPLIT BOLT CONN
extra long description	BUR KS90 SERVIT 12 STR - 10 STR
Long Description	Copper Split Bolt, Cu: 12-10 AWG (Str) (Run & Tap).
Product Type	Mechanical
Special Features	Features: Compact, High Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Season Cracking And Corrosion, The SERVIT Provides Maximum Pressure And Assures A Secure Connection On All Combinations Of Run And Tap Conductors, Conductor Type: Run: Solid Copperweld, Commercial Stranded And Solid Copper, Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Installation Torque: 80 IN-LB, Length: 0.85 IN, Cross Flats: 0.5 IN, Width: 0.38

Manufacturer Information

Brand	BURNDY
GTIN	00781810015254
Manufacturers Part Number	KS90
UPC	781810015254

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KS

Packaging

Carton	1
Weight Per each	0.026

Uses, Certifications, and Standards

Application	For Direct Burial Cables
standard	UL 486A;UL486B