



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTEB232UVISNP 2L F17/25/32 T8 Electronic Ballast 120-277

Keystone Technologies

Catalog Number	KTEB232UVISNP
Manufacturer	Keystone Technologies
Description	2 X F32T8, .88 BF, 120-277V, Instant Start, Electronic
Weight per unit	1.1 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

Ballast Type	Electronic T8
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	N/A
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	2 or 1
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	N/A
Wire Type	Standard Wire Leads

Material, Color, and Finish

Base Type	N/A
color rendering index (cri)	N/A
color temperature	N/A
housing color	N/A

Descriptions

Construction	N/A
Description	2L F17/25/32 T8 ELECTRONIC BALLAST 120-277
extra long description	Key KTEB-232-UV-IS-N-P-CP 60W Max,
Long Description	2 X F32T8, .88 BF, 120-277V, INSTANT START, ELECTRONIC
Product Type	60W Max, 24V Output

Manufacturer Information

Brand	Keystone
GTIN	00890949003558
Manufacturers Part Number	KTEB-232-UV-IS-N-P-DP
UPC	890949003558

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
----------------------	--------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	1.12

Uses, Certifications, and Standards

Energy Star	N
-------------	---