



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTK20 20A 600V Fa Midget Fuse

Bussmann Fuses

Catalog Number	KTK20
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series KTK Fuse, Control Circuits, Lighting Circuit Protection, Meter Circuits, 20 A, Non-Indicating, Ferrule End X Ferrule End, 100 Kaic At 600 V, Melamine Tube, Nickel-Plated Bronze Endcap, 600 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	20 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
interrupt rating	100000 Amp (RMS Symmetrical UL)
Material	Nickel-plated bronze endcapMelamine tube
media	Yes
Voltage Rating	600 VAC

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	20A 600V FA MIDGET FUSE
extra long description	BUSS KTK-20 LIMITRON FAST ACTING FU
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series KTK fuse, Control circuits, Lighting circuit protection, Meter circuits, 20 A, Non-indicating, Ferrule end x ferrule end, 100 kAIC at 600 V, Melamine tube, Nickel-plated bronze endcap, 600 V
Product Type	Limitron Fast Acting Fuse
Special Features	Nickel Plated Bronze Endcap

Manufacturer Information

Brand	Eaton
GTIN	00051712420204
Manufacturers Part Number	KTK-20
UPC	051712420204



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MIDGET FUSES

Type FUZE

Packaging

Carton 10

Weight Per each 0.02

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Facility: Safety and Security Systems

standard CE Marked, RoHS Compliant