



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTLED40T8H096G85 40W Led T8HO 96" 50K Line Volt DBL CNTCT 5550L GLS *Keystone Technologies*

Catalog Number	KTLED40T8H096G85
Manufacturer	Keystone Technologies
Description	40W Led T8 Lamp, 8 Long, Glass Construction, R17D Ho Base, 5000K, 120-277V Input, Internal Driver, Direct Drive
Weight per unit	1.3 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	5500
Nominal Length	96 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	40
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

Descriptions

Construction	Frosted Glass
extra long description	Key KT-LED40T8HO-96G-850-D2 40W LED
Long Description	40W LED T8 Lamp, 8 long, Glass Construction, R17d HO Base, 5000K, 120-277V Input, Internal Driver, Direct Drive
Product Type	40W Led T8 Lamp, 8 Long, Glass Construction, R17D Ho Base, 5

Manufacturer Information

Brand	Keystone
GTIN	00843654140070
Manufacturers Part Number	KT-LED40T8HO-96G-850-D2
UPC	843654140070



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
--------	---

Package	10
---------	----

Weight Per each	1.32
-----------------	------

Uses, Certifications, and Standards

Energy Star	N
-------------	---