



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTLED7T818GC830D 120-277V 7W 30K T8 Led Tube

Keystone Technologies

Catalog Number	KTLED7T818GC830D
Manufacturer	Keystone Technologies
Description	7W Led T8 Tube, Shatter-Proof Coated Glass, Internal Driver, 18", 3000K, 120-277V Input, 25 PCS Cartons, Individually Sleeved
Weight per unit	0.3200 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	750
Nominal Length	18 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	7
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	3000
housing color	N/A

Descriptions

Construction	Frosted Shatterproof Glass
Description	120-277V 7W 30K T8 LED TUBE
extra long description	Key KT-LED7T8-18GC-830-D-CP 7W, 800
Long Description	7W LED T8 Tube, Shatter-Proof Coated Glass, Internal Driver, 18", 3000K, 120-277V Input, 25 pcs cartons, Individually Sleeved
Product Type	7W, 800 Lumen, 18", 240' Beam Angle, Ballast Bypass, Coated

Manufacturer Information

Brand	Keystone
GTIN	00890949009383
Manufacturers Part Number	KT-LED7T8-18GC-830-D-CP
UPC	890949009383



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
--------	---

Package	25
---------	----

Weight Per each	0.32
-----------------	------

Uses, Certifications, and Standards

Energy Star	N
-------------	---