

Specifications



Photo is representative



Eaton KTS-R-10

Eaton Bussmann Series Class RK1 fuse, KTS-R, fast-acting, current limiting fuse, 10 A, rejection style fuse, interrupting rating of 200 kA at 600 Vac

General specifications

PRODUCT NAME	Eaton Bussmann series KTS-R fuse
CATALOG NUMBER	KTS-R-10
UPC	051712417037
EAN	5027590446303
PRODUCT LENGTH/DEPTH	0.8 in
PRODUCT HEIGHT	5 in
PRODUCT WIDTH	0.8 in
PRODUCT WEIGHT	0.13 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked



Powering Business Worldwide

Electrical rating	
AMPERAGE RATING	10 A
INTERRUPT RATING	200 kAIC at 600 Vac
VOLTAGE RATING	600 V

General information	
CLASS	Class RK1
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
SPECIAL FEATURES	70/30 brass end cap

Physical details	
MATERIAL	Melamine glass tube
NUMBER OF ELEMENTS	1
PACKAGING TYPE	Standard

Resources	
CATALOGS	Bussmann Full Line Catalog
	Low Voltage Branch Circuit Fuse Chapter
COMPLIANCE INFORMATION	RoHS Search Tool
MULTIMEDIA	Bussmann series Fuseology
TECHNICAL DATA SHEETS	Bussmann series KTS-R 600 V Class RK1 fuse data sheet no. 1044

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

