



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L11400D 11" 40LB BLK CBL Tie

Abb Installation Products, Inc

Catalog Number	L11400D
Manufacturer	Abb Installation Products, Inc
Description	Intermediate Cable Tie, Black Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant For Indoor and Outdoor Applications, UL/En/CSA62275 Type 2/21 Rated For Ah-2 Plenum, Length Of 279MM (11 Inches), Width Of 3.6MM (0.14 Inches), Thickness Of 1.4MM (0.06 Inches), Bundle Diameter 2MM (0.08 Inches) to 69MM (2.72 Inches), Tensile Strength Rating Of 178 Newtons (40 Pounds), Bulk Pack
Weight per unit	0.0010 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	40;178
------------------	--------

Dimensions and Weight

Length	11.000000000000000
Thickness	0.060000000000000
Width	0.140000000000000

Descriptions

Description	11" 40LB BLK CBL TIE
extra long description	ABB L-11-40-0-D CABLE TIE 40LB 11
Long Description	Intermediate Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 279mm (11 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1.4mm (0.06 Inches), Bundle Diameter 2mm (0.08 Inches) to 69mm (2.72 Inches), Tensile Strength Rating of 178 Newtons (40 Pounds), Bulk Pack
Product Type	Cable Tie 40LB 11 Uv BLK 1-PC Bulk

Manufacturer Information

Brand	Catamount
GTIN	00728494933023
Manufacturers Part Number	L-11-40-0-D
UPC	728494933023

Taxonomies, Classifications, and Categories

Type	INTERMEDIATE
------	--------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 500

Packaging

Carton 500

Weight Per each 0.001

Uses, Certifications, and Standards

standard UL E49405