



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L12HIDE26840D 12W Led Hid Repl 40K Med 1700LM *Keystone Technologies*

Catalog Number	L12HIDE26840D
Manufacturer	Keystone Technologies
Description	Led Hid Replacement Lamp, 12W, E26 Base, 4000K, 120-277V Input, Directdrive
Weight per unit	0.6400 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Ballast Type	N/A
beam angle	360 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	IP64
lumens	1680
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	12
Wire Type	N/A

Material, Color, and Finish

Base Type	E26
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	N/A
Description	12W LED HID REPL 40K MED 1700LM
extra long description	Key KT-LED12HID-E26-840-D-DP 12W, 1
Long Description	LED HID REPLACEMENT LAMP, 12W, E26 BASE, 4000K, 120-277V INPUT, DIRECTDRIVE
Product Type	12W, 1700 Lumen, 50W MH Equiv., IP64, Medium Base

Manufacturer Information

Brand	Keystone
GTIN	00890949019405
Manufacturers Part Number	KT-LED12HID-E26-840-D-DP
UPC	890949019405



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Package 16

Weight Per each 0.64

Uses, Certifications, and Standards

Energy Star Y