



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L12PSHIDE26840DG 6/9/12W Led Hid Repl 40K Med Base 870-1750 LM

Keystone Technologies

Catalog Number	L12PSHIDE26840DG
Manufacturer	Keystone Technologies
Description	Led Hid Replacement Lamp, Power Select 12/9/6W, E26 Base, 4000K, 120-277V Input, Directdrive
Weight per unit	0.0400 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	360 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	N/A
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	12/9/6
Wire Type	N/A

Material, Color, and Finish

Base Type	E26
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	N/A
Description	6/9/12W LED HID REPL 40K MED BASE 870-1750 LM
extra long description	Key KT-LED12PSHID-E26-840-D /G4 LED
Long Description	LED HID Replacement Lamp, Power Select 12/9/6W, E26 Base, 4000K, 120-277V Input, DirectDrive
Product Type	Led Hid Replacement Lamp, Power Select 12/9/6W, E26 Base, 40

Manufacturer Information

Brand	Keystone
GTIN	00843654138107
Manufacturers Part Number	KT-LED12PSHID-E26-840-D /G4
UPC	843654138107



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Package 16

Weight Per each 0.04

Uses, Certifications, and Standards

Energy Star N