



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L12T836GC840DX2 12W Led T8 36" 40K Line DBL/SNGL Ended 1450LM *Keystone Technologies*

| | |
|------------------|---|
| Catalog Number | L12T836GC840DX2 |
| Manufacturer | Keystone Technologies |
| Description | 12W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 3, 4000K, Direct Drive, Single or Double Ended |
| Weight per unit | 0.5600 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 1500 |
| Nominal Length | 36 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Warranty | 5 |
| Wattage | 12 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 4000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | N/A |
| Description | 12W LED T8 36" 40K LINE DBL/SNGL ENDED 1450LM |
| extra long description | Key KT-LED12T8-36GC-840-DX2-CP 12W, |
| Long Description | 12W LED T8 TUBE, SHATTER-PROOF COATED GLASS, 120-277V INPUT, 3, 4000K, DIRECT DRIVE, SINGLE OR DOUBLE ENDED |
| Product Type | 12W, 1450 Lumen, 3', 240' Beam Angle, Ballast Bypass, DLC 4. |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------------------|
| Brand | Keystone |
| GTIN | 00890949019221 |
| Manufacturers Part Number | KT-LED12T8-36GC-840-DX2-CP |
| UPC | 890949019221 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Weight Per each | 0.56 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | Y |
|-------------|---|