



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **L13T5HE48GC85DX2 13W Led T5 48" 50K DBL/Singl Ended Glass Coated** *Keystone Technologies*

Catalog Number	L13T5HE48GC85DX2
Manufacturer	Keystone Technologies
Description	13W Led T5 Tube, Shatter-Proof Coated Glass, Direct Drive, Single or Double Ended, 4 FT., 5000K, 80+Cri, 120-277V Input
Weight per unit	0.0212 (lbs/each)
Product Category	Lighting

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1800
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	5
Wattage	13
Wire Type	N/A

### Material, Color, and Finish

Base Type	G5
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

### Descriptions

Construction	Frosted Shatterproof Glass
Description	13W LED T5 48" 50K DBL/SINGL ENDED GLASS COATED
extra long description	Key KT-LED13T5HE-48GC-850-DX2 13W,
Long Description	13W LED T5 Tube, Shatter-Proof Coated Glass, Direct Drive, Single or Double Ended, 4 ft., 5000K, 80+CRI, 120-277V Input
Product Type	13W, 1800 Lumen, 4', 240' Beam Angle, Ballast Bypass, DLC 4.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654130514
Manufacturers Part Number	KT-LED13T5HE-48GC-850-DX2 /G2
UPC	843654130514

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.0212

## Uses, Certifications, and Standards

Energy Star	N
-------------	---